

ADAP M32-M25-W**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



ADAP series adaptors provide flexibility and versatility infilling unused entries in Ex equipment while maintaining Flameproof Ex d and Increased Safety Ex e explosion protection and IP66/67/68 ingress rate.

General ordering data

Version	ADAP (Klippon Ex adaptor), Adapter, straight, M 32 ,M 25, Brass, nickel-plated
Order No.	1262780000
Type	ADAP M32-M25-W
GTIN (EAN)	4050118088663
Qty.	12 items

ADAP M32-M25-W

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Width	44 mm	Width (inches)	1.7323 inch
Length	21 mm	Length (inches)	0.8268 inch
Net weight	71.72 g		

Temperatures

Operating temperature -50 °C...120 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	69c399a3-d29f-4fa4-b22e-340c0db02257

Certificate numbers cable gland

Identification	II 2G 1D, Ex db IIC Gb, Ex eb IIC Gb, Ex ta IIIC Da	Certificate no. cable gland (ATEX)	TÜV IT 16ATEX 059X
Certificate no. cable gland (IECEX)	IECEX TPS 16.0004X	Certificate no. cable gland (CCC)	2020322313000069
Certificate No. (IECEX)	IECEXTPS16.0004X		

General information

O-Ring	Silicone	Tightening torque	65 Nm
Silicone	Yes	Operating temperature range, max.	120 °C
Operating temperature range, min.	-50 °C	Pitch of thread	1.5 mm
Halogen	halogen-free	Standards	EN 60079-0, EN 60079-1, EN 60079-31, EN 60079-7, IEC 60079-0, IEC 60079-1, IEC 60079-31, IEC 60079-7, GB 12476.1, GB 12476.5, GB 3836.1, GB 3836.2, GB 3836.3
AF size 1	40 mm	Protection degree	IP66
Cable gland	M 32	Basic material	Brass, nickel-plated
External thread	M 32	Internal thread	M 25
Length of thread	16 mm	Explosion protection type	Ex d - flameproof, Ex e - increased safety
Installation guidelines	See assembly instructions		

Classifications

ETIM 8.0	EC000441	ETIM 9.0	EC000441
ETIM 10.0	EC000441	ECLASS 14.0	27-14-08-06
ECLASS 15.0	27-14-08-06		

ADAP M32-M25-W

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Brass lock nuts, nickel-plated



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	SKMU M32 MS	Version	
Order No.	1737020000	SKMU MS (brass locknut), Locknut, M 32, 4 mm, Brass, nickel-plated	
GTIN (EAN)	4008190956493		
Qty.	100 ST		

Nylon flat washer - GWDR



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	GWDR M32-W	Version	
Order No.	1185630000	in closed state, M 32, Nylon 6	
GTIN (EAN)	4050118078329		
Qty.	160 ST		