

IE-FPOZ2EE0001MSJ0SJO-X

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Assembled IE cables, FO patch cable, POF, SC-RJ - SC-RJ,
black

General ordering data

Version	Connecting line, PROFINET, SCRJ IP 20, SCRJ IP 20, 980 µm, Polyethylene, 1 m
Order No.	1273430010
Type	IE-FPOZ2EE0001MSJ0SJO-X
GTIN (EAN)	4050118062885
Qty.	1 items

IE-FPOZ2EE0001MSJ0SJO-X

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Length	1 m	Length (inches)	39.3701 inch
Net weight	31 g		

Temperatures

Storage temperature	Operating temperature	-20 °C...80 °C
Installation temperature		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	67cf1078-beca-4687-860b-dc475a6ec24a

General standards

Connector standard	IEC 61754-24
--------------------	--------------

Standards

Connector standard	IEC 61754-24
--------------------	--------------

Fibre-optic

Fibre type	POF	Attenuation	≤ 160 dB/km at 650 nm
Insertion loss	≤ 1.0 dB	Bandwidth	≥ 100 MHz*km at 650 nm

Cable structure

Sheath diameter	2.2*4.5 mm	Sheathing colour	black
Number of wires	2	Insulation	PE
Material sheath	Polyethylene	Cable layout	ZIPCORD
Core diameter	980 µm		

Mechanical and material properties of cable

Pulling force	≤ 160 N	Halogen	No
Min. bending radius, repetitive	25 mm	Min. bending radius, once only	25 mm
Bending cycles	10.000		

Plug

Plug right	SC-RJ, IP20, male contact, straight, plug, Plastic, unshielded	Plug left	SC-RJ, IP20, male contact, straight, plug, Plastic, unshielded
------------	--	-----------	--

IE-FPOZ2EE0001MSJ0SJO-X

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**Plug, left**

Plug left	SC-RJ, IP20, male contact, straight, plug, Plastic, unshielded
-----------	--

Plug, right

Plug right	SC-RJ, IP20, male contact, straight, plug, Plastic, unshielded
------------	--

Classifications

ETIM 8.0	EC002607	ETIM 9.0	EC002607
ETIM 10.0	EC002607	ECLASS 14.0	27-06-10-03
ECLASS 15.0	27-06-10-03		

Drawings

Detailed drawing

