

PB-DP SUB-D M12 180 OS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly.

General ordering data

Version	SUB-D
Order No.	1274250000
Type	PB-DP SUB-D M12 180 OS
GTIN (EAN)	4050118063974
Qty.	1 items

PB-DP SUB-D M12 180 OS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	14.8 mm	Depth (inches)	0.5827 inch
Height	80.7 mm	Height (inches)	3.1772 inch
Width	31 mm	Width (inches)	1.2205 inch
Net weight	85.36 g		

Temperatures

Humidity	Max. 75% at +25°C, non-condensing
----------	-----------------------------------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6al
REACH SVHC	Lead 7439-92-1
SCIP	a9842d10-2b72-46ab-baf9-9c77c24a2a09

Technical specifications for sub-D connector

Tightening torque	0.3 Nm	Housing main material	ZnAl
Humidity	Max. 75% at +25°C, non-condensing	Protection degree	IP30
Plugging cycles	≥ 200	Data rate	12 MBit/s
Outgoing elbow	180°	Terminating resistor available	No
BUS interface	D-Sub 9-pole, Pin	Plug-in connector and pin assignment	In accordance with the PROFIBUS specification
Interlock	UNC4-40	Temperature range of housing	-20...+70 ° C
BUS, cable interface	M12 B-coded male and female connector, pins 2 and 4 assigned	Programming interface	No

Classifications

ETIM 8.0	EC001132	ETIM 9.0	EC001132
ETIM 10.0	EC001132	ECLASS 14.0	27-44-03-02
ECLASS 15.0	27-44-03-22		

PB-DP SUB-D M12 180 OS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

Wiring diagram

