

SDIK PH2 SL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

General ordering data

Version	Screwdriver, Screwdriver
Order No.	1274720000
Type	SDIK PH2 SL
GTIN (EAN)	4050118073232
Qty.	1 items
Delivery status	Discontinued
Available until	2021-08-06T00:00:00+02:00
Alternative product	SDIK SLIM PH2 X 100

SDIK PH2 SL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Width	218 mm	Width (inches)	8.5827 inch
Diameter	36 mm	Net weight	98 g

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	b28ab223-64ec-44cf-adb0-4dd6ebcae141

Technical data

Description of article	VDE-insulated crosshead screwdriver, Phillips size 2, SlimLine
------------------------	--

Screwing tools

Form	Crosshead	Size	2
Blade length	100 mm	Blade size, crosshead	Gr. PH2

Classifications

ETIM 8.0	EC000144	ETIM 9.0	EC000144
ETIM 10.0	EC000144	ECLASS 14.0	21-04-04-06
ECLASS 15.0	21-04-04-06		

Example of use

