

IE-FM5Z2VO0001MLD0LD0X

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Assembled IE cables, FO patch cable, multimode, LC duplex - LC duplex, orange, Core diameter 50 µm

General ordering data

Version	Pre-assembled patch cable, crossover, LC-Duplex IP 20, LC-Duplex IP 20, 50 µm, PVC, 1 m
Order No.	1276880000
Type	IE-FM5Z2VO0001MLD0LD0X
GTIN (EAN)	4050118066661
Qty.	1 items

IE-FM5Z2VO0001MLD0LD0X

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Length	1 m	Length (inches)	39.3701 inch
Net weight	22 g		

Temperatures

Storage temperature	-25 °C...75 °C	Operating temperature	-5 °C...75 °C
Installation temperature	-5 °C...50 °C		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	67cf1078-beca-4687-860b-dc475a6ec24a

Fibre-optic

Fibre type	GOF, Multimode, OM2	Attenuation	≤ 2.7 dB/km at 850 nm, ≤ 0.7 dB/km at 1300 nm
Bandwidth	≥ 600 MHz*km at 850 nm, ≥ 1200 MHz*km at 1300 nm		

Cable structure

Sheath diameter	3*6 mm	Sheathing colour	orange
Standard designations	I-V(ZN)Y	Material sheath	PVC
Cable layout	ZIPCORD	Primary coating	245.00 µm
Core diameter	50 µm		

Mechanical and material properties of cable

Halogen	yes (PVC cable)	Min. bending radius, repetitive	60 mm
Min. bending radius, once only	30 mm	Resistance to spread of flame	No

Plug

Plug right	LC-Duplex, IP20, male contact, straight, plug, Plastic, unshielded	Plug left	LC-Duplex, IP20, male contact, straight, plug, Plastic, unshielded
------------	--	-----------	--

Plug, left

Plug left	LC-Duplex, IP20, male contact, straight, plug, Plastic, unshielded
-----------	--

Plug, right

Plug right	LC-Duplex, IP20, male contact, straight, plug, Plastic, unshielded
------------	--

Technical data

Classifications

ETIM 8.0	EC002607	ETIM 9.0	EC002607
ETIM 10.0	EC002607	ECLASS 14.0	27-06-10-03
ECLASS 15.0	27-06-10-03		

Drawings

Detailed drawing

