

IE-SCRJ-IP67-POF-100

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



FO SC inserts for plug-in connectors ver.1 / 4 / 14

General ordering data

Version	FO connector, Replacement crimp barrel, IP67 with housing
Order No.	1278430000
Type	IE-SCRJ-IP67-POF-100
GTIN (EAN)	4050118069136
Qty.	100 items

IE-SCRJ-IP67-POF-100

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	26.5 mm	Depth (inches)	1.0433 inch
Height	5.8 mm	Height (inches)	0.2283 inch
Net weight	3 g		

Temperatures

Storage temperature	Operating temperature
Installation temperature	

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	67cf1078-beca-4687-860b-dc475a6ec24a

General data

Description of article	Replacement crimp barrel	Colour	Miscellaneous
Protection degree	IP67 with housing	Fibre type	POF
Insertion loss	≤ 1.0 dB	Connection 1	SCRJ
Connection 2	Rapid connection system: crimping, cutting	Ferrule material	Nickel silver

Classifications

ETIM 8.0	EC001122	ETIM 9.0	EC001122
ETIM 10.0	EC001122	ECLASS 14.0	19-17-01-22
ECLASS 15.0	19-17-01-22		