

ETA 1170 21 6A**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image

As accessories for our wide product portfolio of fuse terminal blocks, we also offer the appropriate fuse links. The portfolio includes device protection fuses (miniature fuses) from 5x20 mm up to 10x38 mm, E 14 to E 18 fuse links, as well as automotive fuses and automatic circuit breakers. Gauge rings for the fuse holders round off the overall portfolio.

General ordering data

Version	Miniature fuse, quick-acting, 6 A, Blade fuse type C
Order No.	1278760000
Type	ETA 1170 21 6A
GTIN (EAN)	4050118091342
Qty.	5 items

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	51.6 mm	Depth (inches)	2.0315 inch
Height	22 mm	Height (inches)	0.8661 inch
Width	9.8 mm	Width (inches)	0.3858 inch
Net weight	9.6 g		

Temperatures

Ambient temperature	-5 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	120 °C		

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	No SVHC above 0.1 wt%

Material data

Colour	black
--------	-------

System specifications

Version	Fuse cartridge
---------	----------------

Additional technical data

Installation advice	Direct mounting	Type of mounting	Plugged
---------------------	-----------------	------------------	---------

General

Installation advice	Direct mounting
---------------------	-----------------

Rating data

Rated voltage	28 V	Nominal current	6 A
---------------	------	-----------------	-----

Classifications

ETIM 8.0	EC002704	ETIM 9.0	EC002704
ETIM 10.0	EC002704	ECLASS 14.0	27-14-20-01
ECLASS 15.0	27-14-20-01		