

**ETA 1170 21 25A****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

As accessories for our wide product portfolio of fuse terminal blocks, we also offer the appropriate fuse links. The portfolio includes device protection fuses (miniature fuses) from 5x20 mm up to 10x38 mm, E 14 to E 18 fuse links, as well as automotive fuses and automatic circuit breakers. Gauge rings for the fuse holders round off the overall portfolio.

**General ordering data**

|            |   |
|------------|---|
| Version    | Miniature fuse, quick-acting, 25 A, Blade fuse type C |
| Order No.  | <a href="#">1278830000</a>                            |
| Type       | ETA 1170 21 25A                                       |
| GTIN (EAN) | 4050118091335   |
| Qty.       | 5 items   |

## Technical data

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Dimensions and weights

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 51.6 mm | Depth (inches)  | 2.0315 inch |
| Height     | 22 mm   | Height (inches) | 0.8661 inch |
| Width      | 9.8 mm  | Width (inches)  | 0.3858 inch |
| Net weight | 9.9 g   |                 |             |

### Temperatures

|                                  |               |                                  |        |
|----------------------------------|---------------|----------------------------------|--------|
| Ambient temperature              | -5 °C...40 °C | Continuous operating temp., min. | -50 °C |
| Continuous operating temp., max. | 120 °C        |                                  |        |

### Environmental Product Compliance

|                        |                       |
|------------------------|-----------------------|
| RoHS Compliance Status | Compliant             |
| REACH SVHC             | No SVHC above 0.1 wt% |

### Material data

|        |       |
|--------|-------|
| Colour | black |
|--------|-------|

### System specifications

|         |                |
|---------|----------------|
| Version | Fuse cartridge |
|---------|----------------|

### Additional technical data

|                     |                 |                  |         |
|---------------------|-----------------|------------------|---------|
| Installation advice | Direct mounting | Type of mounting | Plugged |
|---------------------|-----------------|------------------|---------|

### General

|                     |                 |
|---------------------|-----------------|
| Installation advice | Direct mounting |
|---------------------|-----------------|

### Rating data

|               |      |                 |      |
|---------------|------|-----------------|------|
| Rated voltage | 28 V | Nominal current | 25 A |
|---------------|------|-----------------|------|

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC002704    | ETIM 9.0    | EC002704    |
| ETIM 10.0   | EC002704    | ECLASS 14.0 | 27-14-20-01 |
| ECLASS 15.0 | 27-14-20-01 |             |             |