

CBH 8.1/6.2 NC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Fastening of cables or bundles with ties into electrical switchgears and cabinets.

General ordering data

Version	Cable ties, 6.2 x 8.1 mm, Plastic, 80 N
Order No.	1279200000
Type	CBH 8.1/6.2 NC
GTIN (EAN)	4008 190068820
Qty.	4000 items

CBH 8.1/6.2 NC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	2 mm	Depth (inches)	0.0787 inch
Height	8.1 mm	Height (inches)	0.3189 inch
Width	6.2 mm	Width (inches)	0.2441 inch
Length	2 mm	Length (inches)	0.0787 inch
Net weight	1 g		

Temperatures

Operating temperature range	-40...105 °C
-----------------------------	--------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Installation materials

Max. cable tie width	7.8 mm	UV-resistant	Yes
For re-opening	No	Version	for mounting plate
UL 94 flammability rating	V-2	Operating temperature range, max.	105 °C
Operating temperature range, min.	-40 °C	Halogen	No
Basic material	Plastic	Tensile strength	80 N
Tensile strength (Pound-force)	18 lbf	Diameter of fastening hole	6.5 mm

Important note

Product information	Number of bags in box (pieces): 40 Number of items in bag (pieces): 100 One delivery unit corresponds to one box quantity, and only multiples of the delivery unit can be ordered.
---------------------	--

Classifications

ETIM 8.0	EC000449	ETIM 9.0	EC000449
ETIM 10.0	EC000449	ECLASS 14.0	23-15-25-22
ECLASS 15.0	23-15-25-22		

Drawings

Dimensioned drawing

