

CB-DM 200/4,5 NC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Fastening of cables or bundles with ties into electrical switchgears and cabinets.

General ordering data

Version	Cable ties, 4,5 x 203 mm, Plastic, 220 N
Order No.	1279300000
Type	CB-DM 200/4,5 NC
GTIN (EAN)	4008 190185930
Qty.	100 items
Delivery status	This article will no longer be available in the future.
Available until	2024-05-02T00:00:00+02:00

CB-DM 200/4,5 NC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	2 mm	Depth (inches)	0.0787 inch
Height	203 mm	Height (inches)	7.9921 inch
Width	4.5 mm	Width (inches)	0.1772 inch
Net weight	1.27 g		

Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Installation materials

UV-resistant	No	For re-opening	No
Version	for cable harnesses	UL 94 flammability rating	V-2
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Halogen	No	Cable diameter, max.	50 mm
Basic material	Plastic	Tensile strength	220 N
Bundle diameter, max.	50 mm	Tensile strength (Pound-force)	49 lbf
Bundle diameter, min.	3 mm	Diameter of fastening hole	6.3 mm

Classifications

ETIM 8.0	EC000046	ETIM 9.0	EC000046
ETIM 10.0	EC000046	ECLASS 14.0	27-14-07-02
ECLASS 15.0	27-14-07-02		