

KTB GP XX3815V AB S4 3MM

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Similar to illustration



Abbildung ähnlich

Integrate, expand and customise: The ideal expansion for every application

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

Flange plates

Flange plates in two thicknesses, for easy replacement of pre-assembl

General ordering data

| | |
|------------|--|
| Version | Klippon TB (Terminal Box), flange plate, straight, Height: 376 mm, Width: 117 mm, Depth: 3 mm, Gland plates: top, Bottom, Basic material: Stainless steel 1.4404, Stainless steel 1.4404 (316L), electropolished, silver |
| Order No. | 1281070000 |
| Type | KTB GP XX3815V AB S4 3MM |
| GTIN (EAN) | 4050118071672 |
| Qty. | 1 items |

KTB GP XX3815V AB S4 3MM

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|--------|-----------------|--------------|
| Depth | 3 mm | Depth (inches) | 0.1181 inch |
| Height | 376 mm | Height (inches) | 14.8031 inch |
| Width | 117 mm | Width (inches) | 4.6063 inch |
| Net weight | 1000 g | | |

Temperatures

| | |
|-----------------------|--|
| Operating temperature | |
|-----------------------|--|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

General information

| | | | |
|--------------------|--|-----------------------|---|
| Material thickness | 3 mm | Installation advice | Screw mounting |
| Surface finish | electropolished | Basic material | Stainless steel 1.4404, Stainless steel 1.4404 (316L) |
| Integral fixing | Screwed | Protection class (UL) | Type 3, Type 4X, Type 12 |
| Gland plates | top, Bottom | Flange plate | Yes |
| Areas of use | Transportation, Explosive risk zone | | |

General information on accessories

| | | | |
|--------------------|-----------------|---------------------------------|---|
| Material thickness | 3 mm | Solder eyelet hole diameter (D) | 7 mm |
| Surface finish | electropolished | Basic material | Stainless steel 1.4404, Stainless steel 1.4404 (316L) |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000211 | ETIM 9.0 | EC000211 |
| ETIM 10.0 | EC000211 | ECLASS 14.0 | 27-14-24-21 |
| ECLASS 15.0 | 27-14-24-21 | | |