

**KTB GP 55XX20 CD S4 3MM****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

Abbildung ähnlich

Integrate, expand and customise: The ideal expansion for every application

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

Flange plates

Flange plates in two thicknesses, for easy replacement of pre-assembl

**General ordering data**

|            |                                                                                                                                                                                                                          |
|------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Version    | Klippon TB (Terminal Box), flange plate, straight, Height: 494 mm, Width: 167 mm, Depth: 3 mm, Gland plates: left, right, Basic material: Stainless steel 1.4404, Stainless steel 1.4404 (316L), electropolished, silver |
| Order No.  | <a href="#">1281180000</a>                                                                                                                                                                                               |
| Type       | KTB GP 55XX20 CD S4 3MM                                                                                                                                                                                                  |
| GTIN (EAN) | 4050118071559                                                                                                                                                                                                            |
| Qty.       | 1 items                                                                                                                                                                                                                  |

**KTB GP 55XX20 CD S4 3MM**
**Weidmüller Interface GmbH & Co. KG**

 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)
**Technical data**
**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Dimensions and weights**

|            |        |                 |              |
|------------|--------|-----------------|--------------|
| Depth      | 3 mm   | Depth (inches)  | 0.1181 inch  |
| Height     | 494 mm | Height (inches) | 19.4488 inch |
| Width      | 167 mm | Width (inches)  | 6.5748 inch  |
| Net weight | 1880 g |                 |              |

**Temperatures**

|                       |
|-----------------------|
| Operating temperature |
|-----------------------|

**Environmental Product Compliance**

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

**General information**

|                    |                                        |                       |                                                             |
|--------------------|----------------------------------------|-----------------------|-------------------------------------------------------------|
| Material thickness | 3 mm                                   | Installation advice   | Screw mounting                                              |
| Surface finish     | electropolished                        | Basic material        | Stainless steel 1.4404,<br>Stainless steel 1.4404<br>(316L) |
| Integral fixing    | Screwed                                | Protection class (UL) | Type 3, Type 4X, Type 12                                    |
| Gland plates       | left, right                            | Flange plate          | Yes                                                         |
| Areas of use       | Transportation, Explosive<br>risk zone |                       |                                                             |

**General information on accessories**

|                    |                 |                                 |                                                             |
|--------------------|-----------------|---------------------------------|-------------------------------------------------------------|
| Material thickness | 3 mm            | Solder eyelet hole diameter (D) | 7 mm                                                        |
| Surface finish     | electropolished | Basic material                  | Stainless steel 1.4404,<br>Stainless steel 1.4404<br>(316L) |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000211    | ETIM 9.0    | EC000211    |
| ETIM 10.0   | EC000211    | ECLASS 14.0 | 27-14-24-21 |
| ECLASS 15.0 | 27-14-24-21 |             |             |