

IE-AD-BHS-V14M-RJA

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



PushPull plug-in connector according to IEC
61076-3-117 ver.14 (PROFINET), metal, empty housing

General ordering data

Version	Adapter
Order No.	1302000000
Type	IE-AD-BHS-V14M-RJA
GTIN (EAN)	4050118099638
Qty.	1 items

IE-AD-BHS-V14M-RJA

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E316369

Dimensions and weights

Depth	25.7 mm	Depth (inches)	1.0118 inch
Height	42 mm	Height (inches)	1.6535 inch
Width	24.2 mm	Width (inches)	0.9528 inch
Net weight	61.53 g		

Temperatures

Storage temperature	Operating temperature	-40 °C...70 °C
Installation temperature		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Colour	Miscellaneous	Housing main material	Zinc diecast
Type of mounting	2 screws, M3 (not included)	Protection degree	IP67

General standards

Certificate no. (cULus)	E316369
-------------------------	---------

Classifications

ETIM 8.0	EC001121	ETIM 9.0	EC001121
ETIM 10.0	EC001121	ECLASS 14.0	27-44-03-90
ECLASS 15.0	27-44-03-90		

Installation cut-out

Dimensioned drawing

