



Cross-connection between the VSPC signal contacts can be installed quickly. Cross-connections can be individually separated for the alert function with maximum 10 VSPC R.

General ordering data

Order No.	1309470000
Type	QB 17,8/2
GTIN (EAN)	4050118111934
Qty.	90 items

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	21 mm	Depth (inches)	0.8268 inch
Height	15.5 mm	Height (inches)	0.6102 inch
Width	6 mm	Width (inches)	0.2362 inch
Net weight	1.27 g		

Temperatures

Storage temperature	Operating temperature	-20 °C...55 °C
---------------------	-----------------------	----------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Segment	Measurement - Monitoring - Setting	Colour	yellow
---------	---------------------------------------	--------	--------

Rated data IEC / EN

Rated current I _N	17.5 A
------------------------------	--------

Connection data

Stripping length	6.5 mm	Wire cross-section, solid, max.	1.5 mm ²
Pitch in mm (P)	17.80 mm		

General data

Colour	yellow
--------	--------

Ratings IECEx/ATEX/cUL

cUL certificate	cUL Certificate - pdf/ VSPC.PDF (application/ pdf)
-----------------	--

Classifications

ETIM 8.0	EC002496	ETIM 9.0	EC002496
ETIM 10.0	EC002496	ECLASS 14.0	27-17-90-90
ECLASS 15.0	27-17-90-90		

Drawings

Circuit diagram
