

KLHA M5/20

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image

The comprehensive accessories of the Klippon® Connect portfolio are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms

General ordering data

Version	Busbar (terminal), grey, Height: 130 mm, Depth: 20 mm, Steel
Order No.	1311320000
Type	KLHA M5/20
GTIN (EAN)	4032248152605
Qty.	25 items

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	20 mm	Depth (inches)	0.7874 inch
Height	130 mm	Height (inches)	5.1181 inch
Width	10 mm	Width (inches)	0.3937 inch
Diameter	5.4 mm	Net weight	34.51 g

Temperatures

Ambient temperature	-5 °C...40 °C	Operating temperature	-40 °C...85 °C
---------------------	---------------	-----------------------	----------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	Steel	Surface finish	galvanized
Colour	grey		

Additional technical data

Installation advice	Direct mounting
---------------------	-----------------

Dimensions

Diameter	5.4 mm
----------	--------

General

Installation advice	Direct mounting	Surface finish	galvanized
---------------------	-----------------	----------------	------------

Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-14-11-92
ECLASS 15.0	27-14-11-92		