

**KLHA M5/20****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

The comprehensive accessories of the Klippon® Connect portfolio are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms

**General ordering data**

Version	Busbar (terminal), grey, Height: 130 mm, Depth: 20 mm, Steel
Order No.	<a href="#">1311320000</a>
Type	KLHA M5/20
GTIN (EAN)	4032248152605
Qty.	25 items

**Technical data**

**Approvals**

ROHS	Conform
------	---------

**Dimensions and weights**

Depth	20 mm	Depth (inches)	0.7874 inch
Height	130 mm	Height (inches)	5.1181 inch
Width	10 mm	Width (inches)	0.3937 inch
Diameter	5.4 mm	Net weight	34.51 g

**Temperatures**

Ambient temperature	-5 °C...40 °C	Operating temperature	-40 °C...85 °C
---------------------	---------------	-----------------------	----------------

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Material data**

Basic material	Steel	Surface finish	galvanized
Colour	grey		

**Additional technical data**

Installation advice	Direct mounting
---------------------	-----------------

**Dimensions**

Diameter	5.4 mm
----------	--------

**General**

Installation advice	Direct mounting	Surface finish	galvanized
---------------------	-----------------	----------------	------------

**Classifications**

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-14-11-92
ECLASS 15.0	27-14-11-92		