

STB 36.8/IH/RT WTL6/1

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image**Current and voltage transformer wiring**

Our test disconnect terminal blocks featuring spring and screw connection technology allow you to create all the important converter circuits for measuring current, voltage and power in a safe and sophisticated way.

General ordering data

Version	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 39.8 mm
Order No.	1312540000
Type	STB 36.8/IH/RT WTL6/1
GTIN (EAN)	4050118180992
Qty.	50 items

STB 36.8/IH/RT WTL6/1

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	39.8 mm	Depth (inches)	1.5669 inch
Height	36.8 mm	Height (inches)	1.4488 inch
Width	6 mm	Width (inches)	0.2362 inch
Diameter	6 mm	Net weight	4.93 g

Temperatures

Ambient temperature	-5 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	dce63e23-eea1-4eaa-9071-1c98fc8fa2ea

Material data

Basic material	Polyamide 66	Colour	red
UL 94 flammability rating	V-2		

System specifications

Version	For the terminals
---------	-------------------

Additional technical data

Installation advice	Direct mounting	Type of mounting	when screwed in
---------------------	-----------------	------------------	-----------------

Dimensions

Diameter	6 mm	Plug-in depth	11.1 mm
----------	------	---------------	---------

General

Installation advice	Direct mounting	Operating temperature range, max.	100 °C
---------------------	-----------------	-----------------------------------	--------

Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		