Data sheet

STB 36.8/IH/WS WTL6/1

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image



Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

General ordering data

Version	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 39.8 mm
Order No.	1312560000
Type	STB 36.8/IH/WS WTL6/1
GTIN (EAN)	4050118181203
Qty.	50 items
Delivery status	Discontinued
Last order date	2022-08-31T00:00:00+02:00
Alternative product	STB 21.6/45 GR

Data sheet

STB 36.8/IH/WS WTL6/1

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform

Dimensions and weights

Depth	39.8 mm	Depth (inches)	1.5669 inch
Height	36.8 mm	Height (inches)	1.4488 inch
Width	6 mm	Width (inches)	0.2362 inch
Diameter	6 mm	Net weight	4.98 g

Temperatures

Ambient temperature	-5 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	dce63e23-eea1-4eaa-9071-1c98fc8fa2ea

Material data

Basic material	Polyamide 66	Colour	white
UL 94 flammability rating	V-2		

System specifications

Version	For the terminals

Additional technical data

Installation advice	Direct mounting	Type of mounting	when screwed in

Dimensions

Diameter	6 mm	Plug-in depth	11.1 mm

General

Installation advice	Direct mounting	Operating temperature range, max.	100 °C

Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		