

**KTB RNHD 262615 S4E R****Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26  
D-32758 Detmold  
Germany[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

Abbildung ähnlich

Integrate, expand and customise: The ideal expansion for every application

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

**Rain Covers**

The rain cover provides an ideal, additional level of protection for the enclosure if it is installed in unusual climatic zones with, for instance, very heavy rainfall or extreme levels of direct sunlight.

**General ordering data**

|                     |                                                                                                                                                               |
|---------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Version             | Klippon TB (Terminal Box), Rain hood, Height: 53.9 mm, Width: 265 mm, Depth: 160.5 mm, Basic material: Stainless steel 1.4404 (316L), electropolished, silver |
| Order No.           | <a href="#">1314100000</a>                                                                                                                                    |
| Type                | KTB RNHD 262615 S4E R                                                                                                                                         |
| GTIN (EAN)          | 4050118117455                                                                                                                                                 |
| Qty.                | 1 items                                                                                                                                                       |
| Delivery status     | This article will no longer be available in the future.                                                                                                       |
| Available until     | 2024-10-31T00:00:00+01:00                                                                                                                                     |
| Alternative product | <a href="#">KTB RNHD XX2615 S4E R</a>                                                                                                                         |

**KTB RNHD 262615 S4E R**
**Weidmüller Interface GmbH & Co. KG**

 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)
**Technical data**
**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Dimensions and weights**

|            |          |                 |             |
|------------|----------|-----------------|-------------|
| Depth      | 160.5 mm | Depth (inches)  | 6.3189 inch |
| Height     | 53.9 mm  | Height (inches) | 2.122 inch  |
| Width      | 265 mm   | Width (inches)  | 10.433 inch |
| Net weight | 1455 g   |                 |             |

**Temperatures**

Operating temperature

**Environmental Product Compliance**

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

**General information**

|                |                 |                |                               |
|----------------|-----------------|----------------|-------------------------------|
| Surface finish | electropolished | Basic material | Stainless steel 1.4404 (316L) |
|----------------|-----------------|----------------|-------------------------------|

**General information on accessories**

|                |                 |                |                               |
|----------------|-----------------|----------------|-------------------------------|
| Surface finish | electropolished | Basic material | Stainless steel 1.4404 (316L) |
|----------------|-----------------|----------------|-------------------------------|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000744    | ETIM 7.0    | EC000744    |
| ETIM 8.0    | EC000744    | ETIM 9.0    | EC000744    |
| ETIM 10.0   | EC000744    | ECLASS 9.0  | 27-18-24-05 |
| ECLASS 9.1  | 27-18-92-90 | ECLASS 10.0 | 27-18-24-05 |
| ECLASS 11.0 | 27-18-24-05 | ECLASS 12.0 | 27-18-24-05 |
| ECLASS 13.0 | 27-18-24-05 | ECLASS 14.0 | 27-18-24-05 |
| ECLASS 15.0 | 27-18-24-05 |             |             |