

**VSPC LOCKING CLIP**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



The interlock mechanism on the VSPC Series pluggable arrester delivers extra reliability and an improved permanent contact under strong vibrating conditions.

**General ordering data**

Version	Fastening element, Latches
Order No.	<a href="#">1317340000</a>
Type	VSPC LOCKING CLIP
GTIN (EAN)	4050118121179
Qty.	100 items

**VSPC LOCKING CLIP**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	7.5 mm	Depth (inches)	0.2953 inch
Height	13 mm	Height (inches)	0.5118 inch
Width	17 mm	Width (inches)	0.6693 inch
Net weight	1.34 g		

**Temperatures**

Storage temperature	-40 °C...85 °C	Ambient temperature	-40 °C...70 °C
Operating temperature	-40 °C...70 °C		

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**General data**

Optical function display	No	Segment	Measurement - Monitoring - Setting
Version	Latches	Design	miscellaneous
UL 94 flammability rating	V-0	Colour	yellow
Protection degree	IP20		

**Rated data IEC / EN**

Signalling contact	No
--------------------	----

**Connection data**

Type of connection	Plug / socket
--------------------	---------------

**General data**

Protection degree	IP20	Colour	yellow
-------------------	------	--------	--------

**Guarantee**

Time interval	5 years
---------------	---------

**Classifications**

ETIM 8.0	EC000943	ETIM 9.0	EC000943
ETIM 10.0	EC000943	ECLASS 14.0	27-17-15-01
ECLASS 15.0	27-17-15-01		

**VSPC LOCKING CLIP**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

Circuit diagram