

VSPC LOCKING CLIP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The interlock mechanism on the VSPC Series pluggable arrester delivers extra reliability and an improved permanent contact under strong vibrating conditions.

General ordering data

Version	Fastening element, Latches
Order No.	1317340000
Type	VSPC LOCKING CLIP
GTIN (EAN)	4050118121179
Qty.	100 items

VSPC LOCKING CLIP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	7.5 mm	Depth (inches)	0.2953 inch
Height	13 mm	Height (inches)	0.5118 inch
Width	17 mm	Width (inches)	0.6693 inch
Net weight	1.34 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...70 °C
---------------------	----------------	-----------------------	----------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Optical function display	No	Segment	Measurement - Monitoring - Setting
Version	Latches	Design	miscellaneous
UL 94 flammability rating	V-0	Colour	yellow
Protection degree	IP20		

Connection data

Type of connection	Plug / socket
--------------------	---------------

General data

Protection degree	IP20	Colour	yellow
-------------------	------	--------	--------

Ratings IECEx/ATEX/cUL

cUL certificate	cUL Certificate - pdf/ VSPC.PDF (application/ pdf)
-----------------	--

Guarantee

Time interval	5 years
---------------	---------

Classifications

ETIM 8.0	EC000943	ETIM 9.0	EC000943
ETIM 10.0	EC000943	ECLASS 14.0	27-17-15-01
ECLASS 15.0	27-17-15-01		

VSPC LOCKING CLIP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Circuit diagram