


THM ESO 7 PA GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

Version	Terminal markers, Insert markers, 27 x 6.3 mm, yellow
Order No.	1339580000
Type	THM ESO 7 PA GE
GTIN (EAN)	4050118143799
Qty.	1 items

THM ESO 7 PA GE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Height	27 mm	Height (inches)	1.063 inch
Width	6.3 mm	Width (inches)	0.248 inch
Net weight	286.88 g		

Temperatures

Operating temperature range -40...70 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

Orientation of print	horizontal and vertical		
Width	6.3 mm		
Operating temperature range, max.	70 °C		
Operating temperature range, min.	-40 °C		
Colour	yellow		
Halogen	No		
Basic material	Paper		
Printed characters	without		
Number of markers per packaging unit	2500		
Number of markers per packaging unit	Form of supply	Label reel	
	Number of combinations per packaging unit	1	
	Number of markers per combination	2500	
Number of markers per combination	1 Label reel = 2500 Insert markers		
Operating temperature range	-40...70 °C		
Number per roll	2500		

Classifications

ETIM 8.0	EC000761	ETIM 9.0	EC000761
ETIM 10.0	EC000761	ECLASS 14.0	27-28-11-01
ECLASS 15.0	27-28-11-01		

Drawings

