


SH 4C**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

The comprehensive accessories of the Klippon® Connect portfolio are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms

General ordering data

Version	Busbar support, silver, 85 °C, Width: 15 mm, None, Steel, galvanized, Direct mounting
Order No.	1340870000
Type	SH 4C
GTIN (EAN)	4050118208863
Qty.	10 items

SH 4C

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	25 mm	Depth (inches)	0.9842 inch
Height	25 mm	Height (inches)	0.9842 inch
Width	15 mm	Width (inches)	0.5906 inch
Net weight	24.39 g		

Temperatures

Ambient temperature	-5 °C...40 °C	Operating temperature	-40 °C...85 °C
Continuous operating temp., max.	85 °C		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	Steel, galvanized	Colour	silver
UL 94 flammability rating	None		

Additional technical data

Installation advice	Direct mounting	Type of mounting	Direct mounting
---------------------	-----------------	------------------	-----------------

General

Number of poles	1	Installation advice	Direct mounting
-----------------	---	---------------------	-----------------

Classifications

ETIM 8.0	EC001166	ETIM 9.0	EC001166
ETIM 10.0	EC001166	ECLASS 14.0	27-40-06-07
ECLASS 15.0	27-40-06-07		