

**SH 4C****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

The comprehensive accessories of the Klippon® Connect portfolio are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms

**General ordering data**

Version	Busbar support, silver, 85 °C, Width: 15 mm, None, Steel, galvanized, Direct mounting
Order No.	<a href="#">1340870000</a>
Type	SH 4C
GTIN (EAN)	4050118208863
Qty.	10 items

**SH 4C**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS	Conform
------	---------

**Dimensions and weights**

Depth	25 mm	Depth (inches)	0.9842 inch
Height	25 mm	Height (inches)	0.9842 inch
Width	15 mm	Width (inches)	0.5906 inch
Net weight	24.39 g		

**Temperatures**

Ambient temperature	-5 °C...40 °C	Operating temperature	-40 °C...85 °C
Continuous operating temp., max.	85 °C		

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Material data**

Basic material	Steel, galvanized	Colour	silver
UL 94 flammability rating	None		

**Additional technical data**

Installation advice	Direct mounting	Type of mounting	Direct mounting
---------------------	-----------------	------------------	-----------------

**General**

Number of poles	1	Installation advice	Direct mounting
-----------------	---	---------------------	-----------------

**Classifications**

ETIM 8.0	EC001166	ETIM 9.0	EC001166
ETIM 10.0	EC001166	ECLASS 14.0	27-40-06-07
ECLASS 15.0	27-40-06-07		