

DKB CC DIA 30

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

| | |
|------------|---|
| Version | MetalliCard, Adhesive strip, 30 x , Transparent |
| Order No. | 1341180000 |
| Type | DKB CC DIA 30 |
| GTIN (EAN) | 4050118145618 |
| Qty. | 200 items |

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|----------|---------|-----------------|-------------|
| Depth | 0.01 mm | Depth (inches) | 0.0004 inch |
| Height | 30 mm | Height (inches) | 1.1811 inch |
| Diameter | 30 mm | Net weight | 0.28 g |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -40...160 °C |
|-----------------------------|--------------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

General data

| | | | |
|---|--------------------------------|-------------|--|
| Adhesive | Modified acrylate | | |
| Version | Self-adhesive | | |
| Operating temperature range, max. | 160 °C | | |
| Operating temperature range, min. | -40 °C | | |
| Colour | Transparent | | |
| Basic material | Polyester film | | |
| Printed characters | without | | |
| Number of markers per packaging unit | Form of supply | MetalliCard | |
| Recommended industries compatible printer | Energy, Process | | |
| Number of markers per combination | 1 MetalliCard = Adhesive strip | | |
| Operating temperature range | -40...160 °C | | |

Device markers

| | |
|----------|-------|
| Diameter | 30 mm |
|----------|-------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001288 | ETIM 9.0 | EC001288 |
| ETIM 10.0 | EC001288 | ECLASS 14.0 | 27-28-11-04 |
| ECLASS 15.0 | 27-28-11-04 | | |

Drawings

Example of use

