

**WM4 C I SET****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Workshops and factories prefer well-organised sets of tools. That results in minimal searching and preparation, and that saves money. Weidmüller implements such knowledge when combining products, characterised by good benefits for users and good functionality. Weidmüller Crimp Sets for cutting, stripping and crimping wire end ferrules provide users with practical toolkits.

**General ordering data**

Version	Photovoltaics, Plug-in connector, For crimping tool
Order No.	<a href="#">1344960000</a>
Type	WM4 C I SET
GTIN (EAN)	4050118149036
Qty.	1 items

**WM4 C I SET**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



ROHS Conform

**Dimensions and weights**

Net weight 23 g

**Temperatures**

Continuous operating temp., min. -40 °C Continuous operating temp., max. 85 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**Technical data**

Outer cable diameter, max.	7 mm	Outer cable diameter, min.	5.5 mm
Approvals	TÜV Rheinland (IEC 62852)	Conductor cross-section, max.	6 mm <sup>2</sup>
Conductor cross-section, min.	4 mm <sup>2</sup>	Protection degree	IP65, IP67, IP2x open
Pollution severity	2	Rated voltage	1500 V DC (IEC)
External thread	M 12	Rated current	35 A

**Classifications**

ETIM 8.0	EC002928	ETIM 9.0	EC002928
ETIM 10.0	EC002928	ECLASS 14.0	22-57-02-92
ECLASS 15.0	22-57-02-92		

