

**TOP CASE PREMIUM****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Workshops and factories prefer well-organised sets of tools. That results in minimal searching and preparation, and that saves money. Weidmüller implements such knowledge when combining products, characterised by good benefits for users and good functionality. Weidmüller Crimp Sets for cutting, stripping and crimping wire end ferrules provide users with practical toolkits.

**General ordering data**

Version	Tool case with contents
Order No.	<a href="#">1345320000</a>
Type	TOP CASE PREMIUM
GTIN (EAN)	4050118149739
Qty.	1 items
Packaging	Case

## TOP CASE PREMIUM

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	352 mm	Depth (inches)	13.8582 inch
Height	255 mm	Height (inches)	10.0394 inch
Width	465 mm	Width (inches)	18.3071 inch
Net weight	11290 g		

## Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	7a, 7cl
REACH SVHC	Lead 7439-92-1
SCIP	1eacbb3e-7931-4ebb-9179-f29fd9b50028

## Technical data

Description of article	Tool case
------------------------	-----------

## Assortments

Packaging	Case
-----------	------

## Classifications

ETIM 6.0	EC000149	ETIM 7.0	EC000149
ETIM 8.0	EC000149	ETIM 9.0	EC000149
ETIM 10.0	EC000149	ECLASS 9.0	21-04-50-03
ECLASS 9.1	21-10-01-90	ECLASS 10.0	21-04-50-03
ECLASS 11.0	21-04-50-03	ECLASS 12.0	21-04-50-03
ECLASS 13.0	21-04-50-03	ECLASS 14.0	21-04-50-03
ECLASS 15.0	21-04-50-03		

**TOP CASE PREMIUM**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)



## TOP CASE PREMIUM

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Empty



Workshops and factories prefer well-organised sets of tools. That results in minimal searching and preparation, and that saves money. Weidmüller implements such knowledge when combining products, characterised by good benefits for users and good functionality. Weidmüller Crimp Sets for cutting, stripping and crimping wire end ferrules provide users with practical toolkits.

## General ordering data

Type	TOP CASE	Version	
Order No.	<a href="#">1345330000</a>	Assortment box	
GTIN (EAN)	4050118149913		
Qty.	1 ST		

## Cutting tools



Cutting tools for conductors up to 8 mm, 12 mm, 14 mm and 22 mm outside diameter. The special blade geometry allows pinch-free cutting of copper and aluminium conductors with minimum physical effort. The cutting tools (KT 8 to KT 22) also come with VDE and GS-tested protective insulation up to 1,000 V in accordance with EN/IEC 60900.

## General ordering data

Type	KT 8	Version	
Order No.	<a href="#">9002650000</a>	Cutting tools, Cutting tool for one-hand operation	
GTIN (EAN)	4008190020163		
Qty.	1 ST		

## Tools



Sheathing stripper for PVC cables

## General ordering data

Type	AM 25	Version	
Order No.	<a href="#">9001540000</a>	Tools, Sheathing strippers	
GTIN (EAN)	4008190138271		
Qty.	1 ST		

**TOP CASE PREMIUM**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Accessories**

Type	AM 16	Version
Order No.	<a href="#">9204190000</a>	Tools, Sheathing strippers
GTIN (EAN)	4032248608133	
Qty.	1 ST	
Type	AM 12	Version
Order No.	<a href="#">9030060000</a>	Tools, Sheathing strippers
GTIN (EAN)	4008190337827	
Qty.	1 ST	
Type	STRIPAX	Version
Order No.	<a href="#">9005000000</a>	Tools, Stripping and cutting tool
GTIN (EAN)	4008190072506	
Qty.	1 ST	

**Crimping tools**


Crimping tools for wire end ferrules, with and without plastic collars

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

**General ordering data**

Type	PZ 6 ROTO L	Version
Order No.	<a href="#">1444050000</a>	Pressing tool, Crimping tool for wire-end ferrules, 0.14mm <sup>2</sup> , 6mm <sup>2</sup> ,
GTIN (EAN)	4050118248593	Trapezoidal crimp
Qty.	1 ST	

**Assortment of wire end ferrules with plastic collar**


Box filled with wire end ferrules with plastic collar:

- in Weidmüller colour code
- DIN colour code

**General ordering data**

Type	H-BOX 0,5-2,5QMM DIN	Version
Order No.	<a href="#">9025430000</a>	Assortment of wire end ferrules, Box, Colour code: DIN
GTIN (EAN)	4008190337162	
Qty.	1 ST	

## TOP CASE PREMIUM

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## with LCD Display



The main function of the voltage tester is to establish if voltage is present. A 2-pole voltage tester is the only approved testing instrument that fulfils the requirements of work protection regulations.

- with LCD-Display
- acc. to VDE standard,
- high peak voltage strength
- the right tester for every application

## General ordering data

Type	VT DIGI PRO	Version
Order No.	<a href="#">9918870000</a>	Testing tools, 2-pole voltage tester
GTIN (EAN)	4032248405756	
Qty.	1 ST	

## with LED Display



The main function of the voltage tester is to establish if voltage is present. A 2-pole voltage tester is the only approved testing instrument that fulfils the requirements of work protection regulations.

- with LED-Display
- acc. to VDE standard
- high peak voltage strength
- the right tester for every application

## General ordering data

Type	VT COMBI PRO	Version
Order No.	<a href="#">9918860000</a>	Testing tools, 2-pole voltage tester
GTIN (EAN)	4032248405749	
Qty.	1 ST	

## Tools



- For fast and accurate stripping of cables for damp areas ranging from 8 - 13 mm diameter, e.g. NYM cable, 3 x 1.5 mm<sup>2</sup> to 5 x 2.5 mm<sup>2</sup>
- No need to set cutting depth
- Ideal for working in junction and distribution boxes

## General ordering data

Type	STRIPPER ROUND TOP	Version
Order No.	<a href="#">9918050000</a>	Sheathing strippers
GTIN (EAN)	4032248359165	
Qty.	1 ST	

## TOP CASE PREMIUM

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## VDE insulated telephone pliers



When working with live voltages, you must follow special guidelines and use special tools - tools which have been specially produced and tested for this purpose.

Weidmüller offers a complete line of pliers which comply with national and international testing standards.

All pliers are produced and tested according to DIN EN 60900.

The pliers are ergonomically designed to fit to the hand form, and thus feature an improved hand position. The fingers are not pressed together - this results in less fatigue during operation.

## General ordering data

Type	FRZ S 160	Version
Order No.	<a href="#">9046370000</a>	Pliers
GTIN (EAN)	4032248357673	
Qty.	1 ST	

## VDE-insulated diagonal-cutting pliers



When working with live voltages, you must follow special guidelines and use special tools - tools which have been specially produced and tested for this purpose.

Weidmüller offers a complete line of pliers which comply with national and international testing standards.

All pliers are produced and tested according to DIN EN 60900.

The pliers are ergonomically designed to fit to the hand form, and thus feature an improved hand position. The fingers are not pressed together - this results in less fatigue during operation.

## General ordering data

Type	SE HD 180	Version
Order No.	<a href="#">9046330000</a>	Diagonal-cutting pliers
GTIN (EAN)	4032248357635	
Qty.	1 ST	

## VDE-insulated combination pliers



When working with live voltages, you must follow special guidelines and use special tools - tools which have been specially produced and tested for this purpose.

Weidmüller offers a complete line of pliers which comply with national and international testing standards.

All pliers are produced and tested according to DIN EN 60900.

The pliers are ergonomically designed to fit to the hand form, and thus feature an improved hand position. The fingers are not pressed together - this results in less fatigue during operation.

## TOP CASE PREMIUM

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## General ordering data

Type	KBZ 180	Version	
Order No.	<a href="#">9046290000</a>	Pliers	
GTIN (EAN)	4032248356485		
Qty.	1 ST		

## VDE-insulated flat- and round-nose pliers



up to 1000 V (AC) and 1500 V (DC)

protective insulation acc. to IEC 900. DIN EN 60900

- drop-forged from high-quality special tool steels
- safety handle with ergonomic and non-slip TPE VDE sleeve
- Made from shockproof, heat-and cold-resistant, non-flammable, cadmium-free TPE (thermoplastic elastomer)
- Elastic grip zone and hard core
- Highly-polished surface
- nickel-chromium electro-galvanised coating protects against corrosion

## General ordering data

Type	RZ 160	Version	
Order No.	<a href="#">9046360000</a>	Pliers	
GTIN (EAN)	4032248357666		
Qty.	1 ST		

## Cabinet keys



Crimped conductors are fixed in their respective wiring spaces by screws or a direct plug-in feature. Weidmüller can supply a wide range of tools for screwing.

## General ordering data

Type	CROSS-KEY UNIVERSAL	Version	
Order No.	<a href="#">9918130000</a>	Universal key	
GTIN (EAN)	4032248371112		
Qty.	1 ST		



## TOP CASE PREMIUM

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Combined screwing and cutting tool "Swiftly® CS"

Combined cutting/stripping tool Swiftly® CS and Swiftly® CS set for crimp-free cutting and stripping of copper cables up to 1.5 mm<sup>2</sup> solid and 2.5 mm<sup>2</sup> flexible.



## General ordering data

Type	SWIFTY CS SET	Version
Order No.	<a href="#">9006060000</a>	Cutting and screwing-tool, Cutting tool for one-hand operation
GTIN (EAN)	4032248257638	
Qty.	1 ST	

## Socket wrench sets

Allen key made from fully hardened, high-alloy chromium-vanadium- steel, acc. to DIN ISO 2936 L (DIN 911), high-quality refined surface.



## General ordering data

Type	SK WSD-S 1,5-10,0	Version
Order No.	<a href="#">9008850000</a>	Mounting tool
GTIN (EAN)	4032248266609	
Qty.	1 ST	
Type	SKS 2,0-8,0 MR	Version
Order No.	<a href="#">9008870000</a>	socket wrenches
GTIN (EAN)	4032248266623	
Qty.	1 ST	

## Bit assortment, E6.3

1/4" hexagon drive to DIN 3126, form E6.3 for direct machine connection



## TOP CASE PREMIUM

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## General ordering data

Type	BIT-BOX 11	Version	
Order No.	<a href="#">2748110000</a>	Mounting tool	
GTIN (EAN)	4050118894493		
Qty.	1 ST		

## Set of non-insulated screwdrivers



Weidmüller SoftFinish screwdriver for general uses, blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, matt chrome finish.

## General ordering data

Type	SD SET S2.5-5.5/PH1/2	Version	
Order No.	<a href="#">2749200000</a>	Screwdriver set	
GTIN (EAN)	4050118895506		
Qty.	1 ST		

## Screwdriver Sets



VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

## General ordering data

Type	SDI SET SLIM S3.5-6.5/P...	Version	
Order No.	<a href="#">2749580000</a>	Mounting tool	
GTIN (EAN)	4050118896329		
Qty.	1 ST		

**Accessories****Torque screwdriver**

If you demand effective and exact work, it is essential to use the precise torque. This also guarantees high repetition accuracy.

This is the perfect job for the new Weidmüller torque screwdriver with the ergonomic grip and the unique interchangeable bit system.

- Compact and especially light design
- Torque set with special tool (supplied); an unintended, incorrect setting is ruled out.
- Ergonomic handle sizes matched to the torque range.
- Tools subjected to routine testing and provided with an ID number; 100% quality control with verification and product reference.
- Clicking sound upon reaching the set torque, clearly audible and noticeable, no unnecessary tightening.
- Interchangeable blades made from high-quality wear-resistant tool steel.
- All tools fulfil the accuracy requirements of: EN ISO 6798, BS EN 26789, ASME B107.14M
- Trigger accuracy +/- 6% of the set scale value.

**General ordering data**

Type	DMS MANUELL 0,5-1,7	Version
Order No.	<a href="#">9918370000</a>	Torque screwdriver
GTIN (EAN)	4032248388332	
Qty.	1 ST	