

**PAC-UNIV-HE10-HE10-2M5**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



Similar to illustration

**General ordering data**

|            |                            |
|------------|----------------------------|
| Version    | Pre-assembled cable, PAC   |
| Order No.  | <a href="#">1349630025</a> |
| Type       | PAC-UNIV-HE10-HE10-2M5     |
| GTIN (EAN) | 4099986579088              |
| Qty.       | 1 items                    |

## PAC-UNIV-HE10-HE10-2M5

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Dimensions and weights

|            |       |
|------------|-------|
| Net weight | 103 g |
|------------|-------|

### Temperatures

|                     |             |                       |             |
|---------------------|-------------|-----------------------|-------------|
| Storage temperature | -10...60 °C | Operating temperature | -10...50 °C |
|---------------------|-------------|-----------------------|-------------|

### Environmental Product Compliance

|                        |                       |
|------------------------|-----------------------|
| RoHS Compliance Status | Compliant             |
| REACH SVHC             | No SVHC above 0.1 wt% |

### General Data

|                     |                                 |                       |                                 |
|---------------------|---------------------------------|-----------------------|---------------------------------|
| Cable length        | 2.5 m                           | Suitable for          | Digital signals                 |
| Basic material      | PVC                             | Cable                 | Cable LiYY                      |
| Interface connector | FLAT CABLE CONECTOR<br>HE10 10P | Number of poles, min. | 10-pole                         |
| Outer diameter      | 7 ± 1 mm                        | Connector PLC side    | FLAT CABLE CONECTOR<br>HE10 10P |
| Wire cross-section  | 0.14 mm <sup>2</sup>            |                       |                                 |

### Electrical Data

|                        |                     |   |            |
|------------------------|---------------------|---|------------|
| Total current, max.    | 3 A                 | Permissible current strength per path, max. | 1 A        |
| Rated voltage          | ≤ 60 V DC ≤ 25 V AC | Resistance                                  | ≤ 150 mΩ/m |
| Operating voltage      | ≤ 60 V DC ≤ 25 V AC | Capacity wire / wires                       | 300 pF/m   |
| Capacity wire / shield | 300 pF/m            |   |            |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000237    | ETIM 9.0    | EC000237    |
| ETIM 10.0   | EC000237    | ECLASS 14.0 | 27-24-22-20 |
| ECLASS 15.0 | 27-24-22-20 |             |             |