

## PAC-UNIV-D50F-D50F-4M

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration

### General ordering data

|            |                                                    |
|------------|----------------------------------------------------|
| Version    | Pre-assembled cable, PAC, Cable LiYCY, 14,2 ± 1 mm |
| Order No.  | <a href="#">1349940040</a>                         |
| Type       | PAC-UNIV-D50F-D50F-4M                              |
| GTIN (EAN) | 4099986580534                                      |
| Qty.       | 1 items                                            |

## PAC-UNIV-D50F-D50F-4M

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Dimensions and weights

|            |           |
|------------|-----------|
| Net weight | 1701.45 g |
|------------|-----------|

## Temperatures

|                     |             |                       |             |
|---------------------|-------------|-----------------------|-------------|
| Storage temperature | -10...60 °C | Operating temperature | -10...50 °C |
|---------------------|-------------|-----------------------|-------------|

## Environmental Product Compliance

|                        |                       |
|------------------------|-----------------------|
| RoHS Compliance Status | Compliant             |
| REACH SVHC             | No SVHC above 0.1 wt% |

## General Data

|                     |                      |                       |                  |
|---------------------|----------------------|-----------------------|------------------|
| Cable length        | 4 m                  | Suitable for          | Analogue signals |
| Basic material      | PVC                  | Cable                 | Cable LiYCY      |
| Interface connector | SUB-D FEMALE 50P     | Number of poles, min. | 50-pole          |
| Outer diameter      | 14,2 ± 1 mm          | Connector PLC side    | SUB-D FEMALE 50P |
| Wire cross-section  | 0.25 mm <sup>2</sup> |                       |                  |

## Electrical Data

|                        |                     |                                             |           |
|------------------------|---------------------|---------------------------------------------|-----------|
| Total current, max.    | 3 A                 | Permissible current strength per path, max. | 1 A       |
| Rated voltage          | ≤ 60 Vdc ≤ 25 Vac   | Resistance                                  | ≤ 80 mΩ/m |
| Operating voltage      | ≤ 60 V DC ≤ 25 V AC | Capacity wire / wires                       | 300 pF/m  |
| Capacity wire / shield | 300 pF/m            |                                             |           |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000237    | ETIM 9.0    | EC000237    |
| ETIM 10.0   | EC000237    | ECLASS 14.0 | 27-24-22-20 |
| ECLASS 15.0 | 27-24-22-20 |             |             |