

**PAC-UNIV-D37M-D37F-1M5**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



Similar to illustration

**General ordering data**

|            |  |
|------------|--|
| Version    | Pre-assembled cable, PAC, Cable LiYCY, 12.2 ± 1 mm |
| Order No.  | <a href="#">1349990015</a>                         |
| Type       | PAC-UNIV-D37M-D37F-1M5                             |
| GTIN (EAN) | 4032248176724                                      |
| Qty.       | 1 items  |

## PAC-UNIV-D37M-D37F-1M5

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Dimensions and weights

|            |          |
|------------|----------|
| Net weight | 760.93 g |
|------------|----------|

### Temperatures

|                     |             |                       |          |
|---------------------|-------------|-----------------------|----------|
| Storage temperature | -10...60 °C | Operating temperature | -10...50 |
|---------------------|-------------|-----------------------|----------|

### Environmental Product Compliance

|                        |                                      |
|------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant                            |
| REACH SVHC             | Lead 7439-92-1                       |
| SCIP                   | 4bbf2c0d-0764-4fc8-bb24-9351c28c190d |

### General Data

|                     |                      |                       |                  |
|---------------------|----------------------|-----------------------|------------------|
| Cable length        | 1.5 m                | Suitable for          | Analogue signals |
| Basic material      | PVC                  | Cable                 | Cable LiYCY      |
| Interface connector | SUB-D MALE 37P       | Number of poles, min. | 37-pole          |
| Outer diameter      | 12.2 ± 1 mm          | Connector PLC side    | SUB-D FEMALE 37P |
| Wire cross-section  | 0.25 mm <sup>2</sup> |                       |                  |

### Electrical Data

|                        |                     |   |           |
|------------------------|---------------------|---|-----------|
| Total current, max.    | 3 A                 | Permissible current strength per path, max. | 1 A       |
| Rated voltage          | ≤ 60 Vdc ≤ 25 Vac   | Resistance                                  | ≤ 80 mΩ/m |
| Operating voltage      | ≤ 60 V DC ≤ 25 V AC | Capacity wire / wires                       | 300 pF/m  |
| Capacity wire / shield | 300 pF/m            |   |           |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000237    | ETIM 9.0    | EC000237    |
| ETIM 10.0   | EC000237    | ECLASS 14.0 | 27-24-22-20 |
| ECLASS 15.0 | 27-24-22-20 |             |             |