

## IE-CSPS5VS0350VAPVAP-X

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Assembled IE cables, PROFINET, with push-pull power plug connector according to PROFINET specifications

### General ordering data

Version	System cable, PushPull Power, PushPull Power, PVC, 35 m
Order No.	<a href="#">1350120350</a>
Type	IE-CSPS5VS0350VAPVAP-X
GTIN (EAN)	4050118165579
Qty.	1 items

**IE-CSPS5VS0350VAPVAP-X**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Length	35 m	Length (inches)	1377.9528 inch
Net weight	3905.44 g		

**Temperatures**

Storage temperature	-40 °C...80 °C	Operating temperature	-40 °C...70 °C
Installation temperature	-15 °C...70 °C		

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Electrical properties**

Nominal voltage	24 V	Current-carrying capacity at 50 °C	16 A
-----------------	------	------------------------------------	------

**General standards**

Connector standard	in accordance with PROFINET specification
--------------------	---

**Standards**

Connector standard	in accordance with PROFINET specification
--------------------	---

**Cable structure**

Wire connection cross section AWG, max.	AWG 16	Sheathing colour	grey (similar to RAL 7001)
Cross-section	5*1.5 mm <sup>2</sup>	Shielding	unshielded
Number of wires	5	Insulation	PVC
Sheath diameter, max.	8.1 mm	Material sheath	PVC
Wire material	Non-insulated copper wire		

**Mechanical and material properties of cable**

Halogen	Yes	Min. bending radius, once only	4 x cable diameter
Bending cycles	1 mill.	Resistance to spread of flame	in accordance with IEC 60332-1-2

**Plug**

Plug right	PushPull Power, IP67, female contact, straight, plug, Zinc diecast, unshielded	Plug left	PushPull Power, IP67, female contact, straight, plug, Zinc diecast, unshielded
------------	--	-----------	--

**IE-CSPS5VS0350VAPVAP-X**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data**

**Plug, left**

Plug left	PushPull Power, IP67, female contact, straight, plug, Zinc diecast, unshielded
-----------	---

**Plug, right**

Plug right	PushPull Power, IP67, female contact, straight, plug, Zinc diecast, unshielded
------------	---

**Classifications**

ETIM 8.0	EC003248	ETIM 9.0	EC003248
ETIM 10.0	EC003248	ECLASS 14.0	27-06-01-05
ECLASS 15.0	27-06-01-05		