Data sheet

PAC-UNIV-D9M-F-5M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Similar to illustration

General ordering data

Version	Pre-assembled cable, PAC, Cable LiYCY, 7,8 ± 1 mm
Order No.	1350400050
Type	PAC-UNIV-D9M-F-5M
GTIN (EAN)	4032248186563
Qty.	1 items

Data sheet

PAC-UNIV-D9M-F-5M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform

Dimensions and weights

Net weight	692.6 g

Temperatures

Storage temperature	-10...60 °C	Operating temperature	-10...50

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1
SCIP	4bbf2c0d-0764-4fc8-bb24-9351c28c190d

General Data

Cable length	5 m	Suitable for	Analogue signals
Basic material	PVC	Cable	Cable LiYCY
Interface connector	SUB-D MALE 9P	Number of poles, min.	9-pole
Outer diameter	7,8 ± 1 mm	Connector PLC side	H0.25/10 (FERRULES 0.25mm²)
Wire cross-section	0.25 mm²		

Electrical Data

Total current, max.	3 A	Permissible current strength per path, max.	1 A
Rated voltage	≤ 60 Vdc ≤ 25 Vac	Resistance	≤ 80 mΩ/m
Operating voltage	≤ 60 V DC ≤ 25 V AC	Capacity wire / wires	300 pF/m
Capacity wire / shield	300 pF/m		

Classifications

ETIM 8.0	EC000237	ETIM 9.0	EC000237
ETIM 10.0	EC000237	ECLASS 14.0	27-24-22-20
ECLASS 15.0	27-24-22-20		