

VPU II 0 PV 1500V DC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

**General ordering data**

Version	Surge voltage arrester, Low voltage, Accessories
Order No.	1351480000
Type	VPU II 0 PV 1500V DC
GTIN (EAN)	4050118158632
Qty.	1 items
Delivery status	Discontinued
Available until	2022-12-31T00:00:00+01:00
Alternative product	VPU PV II 0 1500

VPU II 0 PV 1500V DC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	64 mm	Depth (inches)	2.5197 inch
Height	52 mm	Height (inches)	2.0472 inch
Width	17.8 mm	Width (inches)	0.7008 inch
Net weight	89.8 g		

Temperatures

Storage temperature -40 °C...80 °C Operating temperature -40 °C...

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

Optical function display	green = OK; red = arrester is defective - replace	Design	Installation housing; 1TE, Insta IP 20
UL 94 flammability rating	V-0	Colour	orange
Protection degree	IP20	Mounting rail	TS 35

Insulation coordination acc. to EN 50178

Surge voltage category III Pollution severity 2

Photovoltaic technical data

Standards	EN 50539-11	Protection level Up (+/-, -/PE, +/PE)	≤ 5.2 kV
Short-circuit current ISCPV	200 A	Requirements class	Type II
Protection level Up at IN (per module)	≤ 5.2 kV	PV system voltage, max. Ucpv	1500 V
Maximum continuous operating voltage DC UCPV mode +/-, -/PE, +/PE	1500 V		

Rated data IEC / EN

Number of poles	1	Leakage current at Un	30 µA
Rated voltage (DC)	1500 V	PV voltage, acc. to IEC 60364-7-712	<1500 V
Voltage type	DC	Response time / fallback time	≤ 25 ns
Standards	EN 50539-11	Max. continuous voltage, Uc (DC)	1500 V
Discharge current In (8/20µs) wire-PE	12.5 kA	Discharge current Imax (8/20µs) wire-PE	25 kA
Protection level Up at IN (L/N-PE)	≤ 2.6 kV	Integrated back-up fuse	No

Connection data

Type of connection pluggable

VPU II 0 PV 1500V DC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Electrical data

Voltage type	DC
--------------	----

General data

Number of poles	1	Protection degree	IP20
Colour	orange		

Classifications

ETIM 8.0	EC000941	ETIM 9.0	EC000941
ETIM 10.0	EC000941	ECLASS 14.0	27-17-90-90
ECLASS 15.0	27-17-90-90		

Tender specification sheets


Long specification	Spare arrester consisting of V0 material for surge voltage arrester VPU II 1500 VDC series The pluggable high-performance varistors can be exchanged by trained personnel following a failure. Rated voltage: 1500 VDC for PV systems Type: Weidmüller VPU II 0 PV 1500 VDC Order No.: 1351480000	Short specification	Spare arrester for surge voltage arrester VPU II 1500 V DC series The pluggable high-performance varistors can be swapped by trained personnel following a failure. Rated voltage: 1500 V DC for PV systems Type: Weidmüller VPU II 0 PV 1500 V DC Order no.: 1351480000
--------------------	---	---------------------	--

VPU II 0 PV 1500V DC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com



Circuit diagram

VPU II 0 PV 1500V DC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Crosshead screwdriver Phillips



VDE insulated crosshead screwdriver, for Phillips screws, SDIK PH DIN 7438, ISO 8764/2-PH, output to ISO 8764-PH, SoftFinish grip

General ordering data

Type	SDIK PH1 X 80	Version	
Order No.	2749890000	Screwdriver, Blade width (B): 1 mm, 80 mm, Blade thickness (A): 1	
GTIN (EAN)	4050118897098		
Qty.	1 ST		

Slotted screwdriver



VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1. SoftFinish grip

General ordering data

Type	SDIS 1.0X5.5X125	Version	
Order No.	2749850000	Screwdriver, Blade width (B): 5.5 mm, Blade length: 125 mm, Blade thickness (A): 1 mm	
GTIN (EAN)	4050118897050		
Qty.	1 ST		