


ADP 10 S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

Version	Cover profile, RS 100 Transparent, Width: 2000 mm
Order No.	1386220000
Type	ADP 10 S
GTIN (EAN)	4099987167062
Qty.	1 M

ADP 10 S

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	24 mm	Depth (inches)	0.9449 inch
Height	73 mm	Height (inches)	2.874 inch
Width	2000 mm	Width (inches)	78.74 inch
Net weight	433 g		

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Material data

UL 94 flammability rating	V-0	Surface finish	untreated
Basic material	PVC		

General data

Colour	Transparent	Protection degree	IP20 in installed state
Colour chart (similar)	-		

Important note

Product information 3 heights are available for the cover profile and the end plates:
 TS mounting without cover: TS 32 = 45 mm, TS35x7.5 = 40.5 mm
 TS mounting with low cover: TS 32 = 89 mm, TS 35x7.5 = 84.5 mm
 TS mounting with high cover: TS 32 = 121 mm, TS 35x7.5 = 116.5 mm
 Direct mounting, without/low/high cover: 24 / 69 / 99 mm
 Dimensions of the PCB
 Thickness: 1.6 (±0.2) mm, width: 100 (+0.5) mm
 Dimension of the RS section = length of the printed circuit board - 4.5 mm
 Dimension of ADP section = PCB length - 1 mm
 Example:
 PCB length 160 mm, RS = 155.5 mm, ADP = 159 mm"

Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002779
ETIM 10.0	EC002779	ECLASS 14.0	27-19-06-03
ECLASS 15.0	27-19-06-03		