

**SCREWTY-SW13-DM****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**The ideal tool for any application**

Screwty® is the ideal, all-purpose tool for tightening all common sensor and actuator cables. Even difficult-to-reach round plugs are accessible using the Screwty®. A simple turning movement tightens and loosens the connectors without the need for excessive force. The Screwty® is a unique and global solution since it fits with most cables and plugs from other vendors (over 90 %). The Screwty® consists of a handle with a conventional 1/4" adapter. Thus it can be used for all sizes: for M12 and M8 round plug-in connectors, and for M12F and M8F customisable plugs and sockets, as well as for all M23 plugs and sockets.

**General ordering data**

|            |                            |
|------------|----------------------------|
| Version    | Bolting tool               |
| Order No.  | <a href="#">1389190000</a> |
| Type       | SCREWTY-SW13-DM            |
| GTIN (EAN) | 4050118189742              |
| Qty.       | 1 items                    |
| Packaging  | Cardboard box              |

**SCREWTY-SW13-DM**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Dimensions and weights**

|            |          |
|------------|----------|
| Net weight | 226.26 g |
|------------|----------|

**Environmental Product Compliance**

|                        |                       |
|------------------------|-----------------------|
| RoHS Compliance Status | Not affected          |
| REACH SVHC             | No SVHC above 0.1 wt% |

**Screwing tools**

|                      |        |                      |        |
|----------------------|--------|----------------------|--------|
| Torque setting, max. | 1.7 Nm | Torque setting, min. | 0.5 Nm |
|----------------------|--------|----------------------|--------|

**Important note**

|                     |   |
|---------------------|---|
| Product information | Included in delivery: <ul style="list-style-type: none"> <li>• Torque screwdriver 0.5-1.7 Nm + Setting aid</li> <li>• Interchangeable blade AF13</li> </ul> |
|---------------------|---|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000149    | ETIM 9.0    | EC000149    |
| ETIM 10.0   | EC000149    | ECLASS 14.0 | 21-01-90-90 |
| ECLASS 15.0 | 21-01-90-90 |             |             |

## SCREWTY-SW13-DM

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### Screwty® cable gland tool with torque function



The ideal tool for any application  
 Screwty® is the ideal, all-purpose tool for tightening all common sensor and actuator cables. Even difficult-to-reach round plugs are accessible using the Screwty®. A simple turning movement tightens and loosens the connectors without the need for excessive force. The Screwty® is a unique and global solution since it fits with most cables and plugs from other vendors (over 90 %). The Screwty® consists of a handle with a conventional 1/4" adapter. Thus it can be used for all sizes: for M12 and M8 round plug-in connectors, and for M12F and M8F customisable plugs and sockets, as well as for all M23 plugs and sockets.

### General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | SCREWTY SW9                | Version                                    |
| Order No.  | <a href="#">1254630000</a> | Interchangeable blade for cable gland tool |
| GTIN (EAN) | 4050118054194              |  |
| Qty.       | 1 ST                       |  |
| Type       | SCREWTY SW10               | Version                                    |
| Order No.  | <a href="#">1254640000</a> | Interchangeable blade for cable gland tool |
| GTIN (EAN) | 4050118048599              |  |
| Qty.       | 1 ST                       |  |
| Type       | SCREWTY SW12               | Version                                    |
| Order No.  | <a href="#">2598970000</a> | Interchangeable blade for cable gland tool |
| GTIN (EAN) | 4050118781151              |  |
| Qty.       | 1 ST                       |  |
| Type       | SCREWTY SW13               | Version                                    |
| Order No.  | <a href="#">1254650000</a> | Interchangeable blade for cable gland tool |
| GTIN (EAN) | 4050118051834              |  |
| Qty.       | 1 ST                       |  |
| Type       | SCREWTY SW15               | Version                                    |
| Order No.  | <a href="#">1290830000</a> | Interchangeable blade for cable gland tool |
| GTIN (EAN) | 4050118084320              |  |
| Qty.       | 1 ST                       |  |
| Type       | SCREWTY SW17               | Version                                    |
| Order No.  | <a href="#">1254660000</a> | Interchangeable blade for cable gland tool |
| GTIN (EAN) | 4050118051841              |  |
| Qty.       | 1 ST                       |  |
| Type       | SCREWTY SW18               | Version                                    |
| Order No.  | <a href="#">1254670000</a> | Interchangeable blade for cable gland tool |
| GTIN (EAN) | 4050118051858              |  |
| Qty.       | 1 ST                       |  |
| Type       | SCREWTY SW19               | Version                                    |
| Order No.  | <a href="#">1254680000</a> | Interchangeable blade for cable gland tool |
| GTIN (EAN) | 4050118048827              |  |
| Qty.       | 1 ST                       |  |