

**TW PRV8 SDR**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Product image**

The comprehensive accessories of the Klippon® Connect portfolio are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms

**General ordering data**

Version	P-series, Partition plate, grey, 2 mm, Customer-specific printing
Order No.	<a href="#">1389230000</a>
Type	TW PRV8 SDR
GTIN (EAN)	4050118189551
Qty.	10 items

## TW PRV8 SDR

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Depth	59.7 mm	Depth (inches)	2.3504 inch
Height	120 mm	Height (inches)	4.7244 inch
Width	2 mm	Width (inches)	0.0787 inch
Net weight	9.5 g		

## Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	125 °C

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## Material data

Basic material	Polycarbonate	Colour	grey
UL 94 flammability rating	V-0		

## System specifications

Version	Customer-specific printing	Number of levels	8
---------	----------------------------	------------------	---

## Additional technical data

Snap-on	Yes
---------	-----

## Classifications

ETIM 8.0	EC000886	ETIM 9.0	EC000886
ETIM 10.0	EC000886	ECLASS 14.0	27-25-03-01
ECLASS 15.0	27-25-03-01		