

INLAY CC-M 18/52

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

| | |
|------------|----------------------------------|
| Order No. | 1390430000 |
| Type | INLAY CC-M 18/52 |
| GTIN (EAN) | 4050118190861 |
| Qty. | 1 items |

INLAY CC-M 18/52

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 120 mm | Depth (inches) | 4.7244 inch |
| Height | 8 mm | Height (inches) | 0.315 inch |
| Width | 76 mm | Width (inches) | 2.9921 inch |
| Net weight | 66 g | | |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

General data

| | | | |
|---------|--------------------|-------|-------|
| Version | Holder for 4 signs | Width | 76 mm |
|---------|--------------------|-------|-------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001675 | ETIM 9.0 | EC001675 |
| ETIM 10.0 | EC001675 | ECLASS 14.0 | 19-14-90-90 |
| ECLASS 15.0 | 19-14-90-90 | | |

INLAY CC-M 18/52

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

Example of use

