

**THM MT30X 12/6 GE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Similar to illustration**

The THM labels offer brilliant printing quality thanks to the thermal transfer technology. Different materials and the user-friendly printing system under Windows optimise every marking effort.

- High-quality polyester labels in various colours or inexpensive paper labels are available
- Labels are automatically positioned in the printer for perfectly centred prints on each label.

**General ordering data**

|            |  |
|------------|--|
| Version    | THM, Device markers, 6 x 12 mm, yellow |
| Order No.  | <a href="#">1391390000</a>             |
| Type       | THM MT30X 12/6 GE                      |
| GTIN (EAN) | 4050118191523                          |
| Qty.       | 1 items                                |

## THM MT30X 12/6 GE

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Dimensions and weights

|            |          |                 |             |
|------------|----------|-----------------|-------------|
| Depth      | 0.08 mm  | Depth (inches)  | 0.0031 inch |
| Height     | 6 mm     | Height (inches) | 0.2362 inch |
| Width      | 12 mm    | Width (inches)  | 0.4724 inch |
| Net weight | 148.72 g |                 |             |

### Temperatures

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -40...150 °C |
|-----------------------------|--------------|

### Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

### General data

|                                      |  |            |
|--------------------------------------|--|------------|
| Adhesive                             | Acrylate   |            |
| Printing method                      | Thermal transfer   |            |
| Version                              | Self-adhesive, halogen-free  |            |
| Width                                | 12 mm  |            |
| UL 94 flammability rating            | V-0  |            |
| Operating temperature range, max.    | 150 °C   |            |
| Operating temperature range, min.    | -40 °C   |            |
| Colour                               | yellow   |            |
| Halogen                              | No   |            |
| Basic material                       | Polyester  |            |
| Printed characters                   | without  |            |
| Number of markers per packaging unit | Form of supply   | Label reel |
| compatible printer                   | <a href="#">THM MULTIMARK</a> , <a href="#">THM MULTIMARK PLUS</a> |            |
| Number of markers per combination    | 1 Label reel = Device markers                                      |            |
| Operating temperature range          | -40...150 °C   |            |
| Number per roll                      | 10000  |            |

### Device markers

|         |    |
|---------|----|
| Halogen | No |
|---------|----|

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001288    | ETIM 9.0    | EC001288    |
| ETIM 10.0   | EC001288    | ECLASS 14.0 | 27-28-11-04 |
| ECLASS 15.0 | 27-28-11-04 |             |             |

**Drawings**

**Similar to illustration**

---

