


**AP DK4Q BL****Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26  
D-32758 Detmold  
Germany[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Similar to illustration

Partition plates and end plates are essential accessories for terminal blocks. Partition plates provide optical and electrical separation of different potentials and functional groups, increasing safety and ensuring a clear structure inside the control cabinet. End plates close the terminal block row on the sides, protect against contact with live parts, and ensure a clean, stable finish. Both components are precisely matched to the respective Weidmüller terminal block series, contributing to safe, compliant, and professional wiring.

**General ordering data**

|                     |                                                                                       |
|---------------------|---------------------------------------------------------------------------------------|
| Version             | End plate for terminals, blue, Height: 54 mm, Width: 1.5 mm, V-2, PA 66, Snap-on: Yes |
| Order No.           | <a href="#">1397180000</a>                                                            |
| Type                | AP DK4Q BL                                                                            |
| GTIN (EAN)          | 4008190171728                                                                         |
| Qty.                | 20 items                                                                              |
| Delivery status     | This article will no longer be available in the future.                               |
| Available until     | 2026-06-30T00:00:00+02:00                                                             |
| Alternative product | <a href="#">AP DK4Q</a>                                                               |

## AP DK4Q BL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Dimensions and weights

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 43.5 mm | Depth (inches)  | 1.7126 inch |
| Height     | 54 mm   | Height (inches) | 2.126 inch  |
| Width      | 1.5 mm  | Width (inches)  | 0.0591 inch |
| Net weight | 3 g     |                 |             |

## Temperatures

|                                  |                |                                  |               |
|----------------------------------|----------------|----------------------------------|---------------|
| Storage temperature              | -25 °C...55 °C | Ambient temperature              | -5 °C...40 °C |
| Continuous operating temp., min. | -50 °C         | Continuous operating temp., max. | 100 °C        |

## Environmental Product Compliance

|                          |                             |                 |  |
|--------------------------|-----------------------------|-----------------|--|
| RoHS Compliance Status   | Compliant without exemption |                 |  |
| REACH SVHC               | No SVHC above 0.1 wt%       |                 |  |
| Product Carbon Footprint | Cradle to gate              | 0.027 kg CO2eq. |  |

## Material data

|                           |       |        |      |
|---------------------------|-------|--------|------|
| Basic material            | PA 66 | Colour | blue |
| UL 94 flammability rating | V-2   |        |      |

## System specifications

|         |           |
|---------|-----------|
| Version | End plate |
|---------|-----------|

## Additional technical data

|         |     |                     |                 |
|---------|-----|---------------------|-----------------|
| Snap-on | Yes | Installation advice | Direct mounting |
|---------|-----|---------------------|-----------------|

## General

|                     |                 |
|---------------------|-----------------|
| Installation advice | Direct mounting |
|---------------------|-----------------|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000886    | ETIM 9.0    | EC000886    |
| ETIM 10.0   | EC000886    | ECLASS 14.0 | 27-25-03-01 |
| ECLASS 15.0 | 27-25-03-01 |             |             |