

PLUG VPU

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Extensive accessories round off the product range

General ordering data

| | |
|------------|----------------------------|
| Version | VPU series, Accessories |
| Order No. | 1402570000 |
| Type | PLUG VPU |
| GTIN (EAN) | 4050118204360 |
| Qty. | 10 items |

PLUG VPU

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 21.5 mm | Depth (inches) | 0.8465 inch |
| Height | 8 mm | Height (inches) | 0.315 inch |
| Width | 11.6 mm | Width (inches) | 0.4567 inch |
| Net weight | 1.96 g | | |

Temperatures

Storage temperature Operating temperature -40 °C...70 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Connection data, remote alert

| | | | |
|--|----------------------|--|---------------------|
| Cross-section for connected wire, solid core, min. | 0.14 mm ² | Stripping length | 8 mm |
| Connection type | PUSH IN | Cross-section for connected wire, solid core, max. | 1.5 mm ² |

General data

Segment Power distribution Version Plug, printed
 Colour black

Rated data IEC / EN

Rated voltage (AC) 250 V

General data

Colour black

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001627 | ETIM 9.0 | EC001627 |
| ETIM 10.0 | EC001627 | ECLASS 14.0 | 27-17-90-90 |
| ECLASS 15.0 | 27-17-90-90 | | |