


KLBUE 3-8 RC TS27**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

With our wide range of KLBÜ shield connections, you can achieve flexible and self-adjusting shield contacting and ensure error-free plant operation.

General ordering data

Version	Clamping yoke, Clamping yoke for shield connection, PA 66 GF 30
Order No.	1403070000
Type	KLBUE 3-8 RC TS27
GTIN (EAN)	4050118204780
Qty.	1 items

KLBUE 3-8 RC TS27

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	50 mm	Depth (inches)	1.9685 inch
Height	67.5 mm	Height (inches)	2.6575 inch
Width	35 mm	Width (inches)	1.378 inch
Net weight	61.19 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
Continuous operating temp., min.	-25 °C	Continuous operating temp., max.	105 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	6fc8563f-82a2-46cf-b3da-0e2c7ddd4382

Material data

Basic material	PA 66 GF 30	Colour	black, Silver grey
UL 94 flammability rating	V-0		

System specifications

Version	For a shield connection, With resistor	End cover plate required	No
Mounting rail	TS 27		

Additional technical data

Installation advice	Direct mounting	Explosion-tested version	No
Type of mounting	Snap-on		

Conductors for clamping (rated connection)

Stripping length	22 mm	Type of connection	Spring connection
Number of connections	1	Cable diameter, max.	8 mm
Cable diameter, min.	3 mm	Connection cross-section, stranded, max.	8 mm ²
Connection cross-section, stranded, min. 3 mm ²			

General

Installation advice	Direct mounting	Mounting rail	TS 27
---------------------	-----------------	---------------	-------

Rating data

Rated cross-section	8 mm ²	Rated voltage	230 V
---------------------	-------------------	---------------	-------

KLBUE 3-8 RC TS27

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Classifications

ETIM 8.0	EC002020	ETIM 9.0	EC002020
ETIM 10.0	EC002020	ECLASS 14.0	27-25-01-20
ECLASS 15.0	27-25-01-20		

Drawings

