

IE-CSPD5US0150VAPVAP-X

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

Version	System cable, PushPull Power, PushPull Power, PUR, 15 m
Order No.	1403680150
Type	IE-CSPD5US0150VAPVAP-X
GTIN (EAN)	4050118205428
Qty.	1 items

IE-CSPD5US0150VAPVAP-X

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Length	15 m	Length (inches)	590.5512 inch
Net weight	2060 g		

Temperatures

Storage temperature	-50 °C...80 °C	Operating temperature	-40 °C...80 °C
Installation temperature	-40 °C...80 °C		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Electrical properties

Nominal voltage	24 V	Current-carrying capacity at 50 °C	16 A
-----------------	------	------------------------------------	------

General standards

Connector standard	in accordance with PROFINET specification
--------------------	---

Standards

Connector standard	in accordance with PROFINET specification
--------------------	---

Cable structure

Wire connection cross section AWG, max.	AWG 16	Sheathing colour	grey (similar to RAL 7001)
Cross-section	5*1.5 mm ²	Shielding	unshielded
Number of wires	5	Insulation	TPE
Sheath diameter, max.	9 mm	Material sheath	PUR
Wire material	Non-insulated copper wire		

Mechanical and material properties of cable

Halogen	No	Min. bending radius, once only	5 x cable diameter
Resistance to spread of flame	in accordance with IEC 60332-1-2		

Plug

Plug right	PushPull Power, IP67, female contact, straight, plug, Zinc diecast, unshielded	Plug left	PushPull Power, IP67, female contact, straight, plug, Zinc diecast, unshielded
------------	--	-----------	--

IE-CSPD5US0150VAPVAP-X

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Plug, left

Plug left	PushPull Power, IP67, female contact, straight, plug, Zinc diecast, unshielded
-----------	---

Plug, right

Plug right	PushPull Power, IP67, female contact, straight, plug, Zinc diecast, unshielded
------------	---

Classifications

ETIM 8.0	EC003248	ETIM 9.0	EC003248
ETIM 10.0	EC003248	ECLASS 14.0	27-06-01-05
ECLASS 15.0	27-06-01-05		