

**INLAY CC-M 70/48**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

---

**General ordering data**

|            |                                  |
|------------|----------------------------------|
| Order No.  | 1415940000                       |
| Type       | <a href="#">INLAY CC-M 70/48</a> |
| GTIN (EAN) | 4050118217247                    |
| Qty.       | 1 items                          |

**INLAY CC-M 70/48**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Depth      | 120 mm | Depth (inches)  | 4.7244 inch |
| Height     | 8 mm   | Height (inches) | 0.315 inch  |
| Width      | 76 mm  | Width (inches)  | 2.9921 inch |
| Net weight | 65 g   |                 |             |

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**General data**

|                                   |                    |                                   |        |
|-----------------------------------|--------------------|-----------------------------------|--------|
| Version                           | Holder for 3 signs | Width                             | 76 mm  |
| Operating temperature range, max. | 130 °C             | Operating temperature range, min. | -55 °C |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001675    | ETIM 7.0    | EC001675    |
| ETIM 8.0    | EC001675    | ETIM 9.0    | EC001675    |
| ETIM 10.0   | EC001675    | ECLASS 9.0  | 19-14-92-90 |
| ECLASS 9.1  | 19-14-92-90 | ECLASS 10.0 | 19-14-92-90 |
| ECLASS 11.0 | 19-14-90-90 | ECLASS 12.0 | 19-14-90-90 |
| ECLASS 13.0 | 19-14-90-90 | ECLASS 14.0 | 19-14-90-90 |
| ECLASS 15.0 | 19-14-90-90 |             |             |

**Drawings**

**Example of use**

---

---

---

---