

INLAY CC-M 58/35

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

Order No.	1415950000
Type	INLAY CC-M 58/35
GTIN (EAN)	4050118217254
Qty.	1 items

INLAY CC-M 58/35

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	120 mm	Depth (inches)	4.7244 inch
Height	8 mm	Height (inches)	0.315 inch
Width	76 mm	Width (inches)	2.9921 inch
Net weight	74 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Version	Holder for 10 signs	Width	76 mm
Operating temperature range, max.	130 °C	Operating temperature range, min.	-55 °C

Classifications

ETIM 8.0	EC001675	ETIM 9.0	EC001675
ETIM 10.0	EC001675	ECLASS 14.0	19-14-90-90
ECLASS 15.0	19-14-90-90		

INLAY CC-M 58/35

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

Example of use

