

**INLAY CC-M 58/35**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



**General ordering data**

Order No.	1415950000
Type	<a href="#">INLAY CC-M 58/35</a>
GTIN (EAN)	4050118217254
Qty.	1 items

**INLAY CC-M 58/35**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS	Conform
------	---------

**Dimensions and weights**

Depth	120 mm	Depth (inches)	4.7244 inch
Height	8 mm	Height (inches)	0.315 inch
Width	76 mm	Width (inches)	2.9921 inch
Net weight	74 g		

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**General data**

Version	Holder for 10 signs	Width	76 mm
Operating temperature range, max.	130 °C	Operating temperature range, min.	-55 °C

**Classifications**

ETIM 8.0	EC001675	ETIM 9.0	EC001675
ETIM 10.0	EC001675	ECLASS 14.0	19-14-90-90
ECLASS 15.0	19-14-90-90		

**INLAY CC-M 58/35**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)

**Example of use**

