


H35,0/32 S BE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

- Polypropylene conical cable entry funnel
 - Heat-resistant up to 105°C
- For conductors from 0.5 – 10.0 mm² (AWG 20-7)
Material: E-Cu, tin galvanised
Dimensional tolerance acc. to DIN 46228 sect. 4

General ordering data

Version	Wire-end ferrule, Standard, 21 mm, 18 mm, beige
Order No.	1418340000
Type	H35,0/32 S BE
GTIN (EAN)	4050118221725
Qty.	50 items
Packaging	loose

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E354986
Certificate no. (cULus)	E499744

Dimensions and weights

Net weight	2.02 g
------------	--------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	Wire-end ferrules with plastic collar, special size, colour beige	Version	Standard
------------------------	---	---------	----------

Wire-end ferrules

Contact surface diameter (D1)	8.3 mm	Contact surface length (L2)	18 mm
Collar diameter (D2)	12.7 mm	Plastic collar thickness (S2)	0.4 mm
L1 in mm	32.00 mm	Wire connection cross section AWG, max.	AWG 2
Metal sleeve thickness (S1)	0.2 mm	Stripping length	21 mm
Conductor cross-section	35 mm ²	Colour code	Weidmueller

Classifications

ETIM 8.0	EC000005	ETIM 9.0	EC000005
ETIM 10.0	EC000005	ECLASS 14.0	27-40-02-01
ECLASS 15.0	27-40-02-01		

Drawing

