

**HSS-HF 19.1-38.1EL W10M**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

**General ordering data**

Version	Conductor and cable markers, 19.1 - 38.1 mm, white
Order No.	<a href="#">1423420000</a>
Type	HSS-HF 19.1-38.1EL W10M
GTIN (EAN)	4050118227451
Qty.	1 items

**HSS-HF 19.1-38.1EL W10M**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	1.5 mm	Depth (inches)	0.0591 inch
Width	60.5 mm	Width (inches)	2.3819 inch
Length	10000 mm	Length (inches)	393.7 inch
Net weight	943 g		

**Temperatures**

Operating temperature range -55...105 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**General data**

Type of printing	neutral	Width	60.5 mm
Operating temperature range, max.	105 °C	Operating temperature range, min.	-55 °C
Colour	white	Halogen	No
Length	10000 mm	Basic material	Polyolefine
Printed characters	without	compatible printer	<a href="#">THM MULTIMARK</a> , <a href="#">THM MULTIMARK PLUS</a>
Operating temperature range	-55...105 °C	Number per roll	1

**Conductor and cable markers**

Halogen	No	Conductor cross-section, max.	240 mm <sup>2</sup>
Conductor cross-section, min.	70 mm <sup>2</sup>	Conductor O.D., max.	38.1 mm
Conductor O.D., min.	19.1 mm	Rate of shrinkage	2:1
Recommended shrinking temperature	90 °C	Conductor O.D.	19.1 - 38.1 mm
Cross-section for connected wire	70 - 240 mm <sup>2</sup>		

**Classifications**

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

## HSS-HF 19.1-38.1EL W10M

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

# Accessories

## Ink ribbons



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

### General ordering data

Type	RIBBON HSS HF EL 40/300...	Version	
Order No.	<a href="#">1426210000</a>	Ink ribbon	
GTIN (EAN)	4050118228823		
Qty.	1 ST		

## THM MULTIMARK




These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

### General ordering data

Type	MULTIMARK ROLLER 115	Version	
Order No.	<a href="#">1357420000</a>		
GTIN (EAN)	4050118160314		
Qty.	1 ST		
Type	MULTIMARK ROLLER 30	Version	
Order No.	<a href="#">1357430000</a>		
GTIN (EAN)	4050118160253		
Qty.	1 ST		

## THM MULTIMARK PLUS



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

## HSS-HF 19.1-38.1EL W10M

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

### General ordering data

Type	MULTIMARK PLUS ROLLER 1...	Version
Order No.	<a href="#">2672590000</a>	
GTIN (EAN)	4050118708097	
Qty.	1 ST	