

IE-FSMZ2LY0015MLD0LD0-X

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Assembled IE cables, FO

General ordering data

Version	Pre-assembled patch cable, crossover, LC-Duplex IP 20, LC-Duplex IP 20, 9 µm, LSZH, 15 m
Order No.	1433950150
Type	IE-FSMZ2LY0015MLD0LD0-X
GTIN (EAN)	4050118694246
Qty.	1 items

IE-FSMZ2LY0015MLD0LD0-X

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Length	15 m	Length (inches)	590.5512 inch
Net weight	109.12 g		

Temperatures

Storage temperature	-25 °C...75 °C	Operating temperature	-5 °C...75 °C
Installation temperature	-5 °C...50 °C		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Fibre-optic

Fibre type Singlemode, OS1

Cable structure

Sheath diameter	3*6 mm	Sheathing colour	yellow
Standard designations	I-V(ZN)Y	Material sheath	LSZH
Cable layout	ZIPCORD	Primary coating	245.00 µm
Core diameter	9 µm		

Plug

Plug right	LC-Duplex, IP20, male contact, straight, plug, Plastic, unshielded	Plug left	LC-Duplex, IP20, male contact, straight, plug, Plastic, unshielded
------------	--	-----------	--

Plug, left

Plug left LC-Duplex, IP20, male contact, straight, plug, Plastic, unshielded

Plug, right

Plug right LC-Duplex, IP20, male contact, straight, plug, Plastic, unshielded

Classifications

ETIM 8.0	EC002607	ETIM 9.0	EC002607
ETIM 10.0	EC002607	ECLASS 14.0	27-06-10-03
ECLASS 15.0	27-06-10-03		

Drawings

Detailed drawing

