

**IE-FM5Z2LO0001MST0ST0-X**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



Assembled IE cables, FO

**General ordering data**

Version	Patch cable, ST IP 20, ST IP 20, 50 µm, LSZH, 1 m
Order No.	<a href="#">1433990010</a>
Type	IE-FM5Z2LO0001MST0ST0-X
GTIN (EAN)	4050118242768
Qty.	1 items

## IE-FM5Z2LO0001MST0ST0-X

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Length	1 m	Length (inches)	39.3701 inch
Net weight	35.2 g		

### Temperatures

Storage temperature	Operating temperature	-20 °C...70 °C
Installation temperature		

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Cable specific standards

Specification for twisted-pair device connection cables	IEC 61156-6, DIN EN 50288-4-2	Specification for checking the symmetrical communication cabling	IEC 61935-3
---------------------------------------------------------	-------------------------------	------------------------------------------------------------------	-------------

### General standards

Connector standard	IEC 60874-10
--------------------	--------------

### Standards

Connector standard	IEC 60874-10
--------------------	--------------

### Fibre-optic

Fibre type	GOF, Multimode, OM2	Attenuation	≤2.5 dB/km at 850 nm, ≤ 0.7 dB/km at 1300 nm
Bandwidth	≥ 500 MHz*km at 850 nm, ≥ 500 MHz*km at 1300 nm		

### Cable structure

Sheath diameter	2.8 * 5.7 mm	Sheathing colour	orange
Standard designations	I-V(ZN)H	Material sheath	LSZH
Cable layout	ZIPCORD	Primary coating	245.00 µm
Core diameter	50 µm		

### Mechanical and material properties of cable

Halogen	No	Min. bending radius, repetitive	56 mm
Min. bending radius, once only	28 mm		

### Plug

Plug right	ST, IP20, male contact, straight, plug, Plastic, unshielded	Plug left	ST, IP20, male contact, straight, plug, Plastic, unshielded
------------	-------------------------------------------------------------	-----------	-------------------------------------------------------------

## IE-FM5Z2LO0001MST0ST0-X

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Plug, left

Plug left	ST, IP20, male contact, straight, plug, Plastic, unshielded
-----------	-------------------------------------------------------------

### Plug, right

Plug right	ST, IP20, male contact, straight, plug, Plastic, unshielded
------------	-------------------------------------------------------------

### Classifications

ETIM 8.0	EC002607	ETIM 9.0	EC002607
ETIM 10.0	EC002607	ECLASS 14.0	27-06-10-03
ECLASS 15.0	27-06-10-03		

**Drawings**

**Detailed drawing**

