

IE-FC-SP-1ST/1D9/1D25**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



FrontCom® Vario integrates multiple functions in only one single frame. The system is easy to install and you can select from a wide range of data, signal and power modules. In addition to being extremely compact, FrontCom® Vario offers a number of unique product features that will make your project planning and work activities secure, fast and future-proof. Furthermore, the FrontCom® Vario system has an attractive housing design that, by the way, offers highest impact-resistance and fully meets the requirements of IP 65 protection class.

General ordering data

Version	FrontCom, Insert plate, shielded
Order No.	1450580000
Type	IE-FC-SP-1ST/1D9/1D25
GTIN (EAN)	4050118255485
Qty.	1 items

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E223801

Dimensions and weights

Height	23 mm	Height (inches)	0.9055 inch
Width	51.5 mm	Width (inches)	2.0276 inch
Length	90.5 mm	Length (inches)	3.563 inch
Net weight	20.5 g		

Temperatures

Storage temperature	Operating temperature	-40 °C...70 °C
Installation temperature		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	Potassium perfluorobutane sulfonate 29420-49-3
SCIP	8a473a8a-33d4-43 18-8088-c28f0 19e7f77

General data

Product type	Insert plate, shielded	Material	Polycarbonate PC
--------------	------------------------	----------	------------------

Inserts

Insert, signal, D-Sub, 25-pole	1	Insert, data	1
Signal insert D-Sub 9-pole / VGA / HDMI	1		

General standards

Certificate No. (cURus)	E223801	Certificate No. (DNV)	TAA000022B
Certificate No. (CSA)	2000039-80039714		

Classifications

ETIM 8.0	EC000456	ETIM 9.0	EC000456
ETIM 10.0	EC000456	ECLASS 14.0	27-18-28-92
ECLASS 15.0	27-18-28-92		

Dimensioned drawing

